



GB29T4W, Mechanical Grounding Connector, Cable to Bar, Tin Plated

By Burndy
Catalog # [GB29T4W](#)



Mechanical Grounding Connector, Cable to 1/4" - 1/2" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud, 1.5 IN Width Hot Tin Dipped.

Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GB separates cable from bar
- One-wrench installation
- UL467 Listed, Suitable for Direct Burial in earth or concrete

General

Catalog Number	GB29T4W
Installation Torque	480 lb-in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	N
Plating Type	Tin - Hot Dipped
UPC	781810117286
UPC 14 Digit GTIN	00781810117286

Dimensions

Dimension - D inch	1.08 in
Dimension - Height inch	2.32 in
Dimension - Height mm	59 mm
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Pad Width inch	1.78 in
Dimension - Width fraction	1-22/25 in
Dimension - Width inch	1.88in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GB_Lineart](#)
[Sales Drawings - sc091657-01](#)
[Specifications - GB29T4W](#)



A Hubbell brand