



GB29WT9, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # GB29WT9



2/0 SOL - 250 kcmil Cu Bar Size: 1/4" Thick.

General

Catalog Number	GB29WT9
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Tin - Hot Dipped
UPC	621945138971
UPC 12 Digit	6219451389711

Dimensions

Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.44 in
Dimension - Width fraction	1-47/50 in
Dimension - Width inch	1.94 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GB29WT9_MODEL-STEP](#)
- [3D Models - GB29WT9_MODEL-IGES](#)
- [3D Models - GB29WT9_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GB_Lineart](#)
- [Sales Drawings - 50089501](#)
- [Specifications - GB29WT9](#)