



GBG28G2, Copper Ground Connector

By Burndy
Catalog # [GBG28G2](#)



Copper Ground Connector CU CABLE: 8 AWG (SOL) - 4 AWG (STR) 5/16" Stud.

General

Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810343623
UPC 12 Digit	7818103436233

Dimensions

Dimension - B Length inch	1.19 in
Dimension - Width fraction	9 in
Dimension - Width inch	9.00 in

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	4 AWG-4/0 AWG
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	4 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10035118](#)



A proud member of the Hubbell Family.