



GBM26T8, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GBM26T8](#)



Mechanical Grounding Connector, Cable to 1/4" - 1" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud.

General

Catalog Number	GBM26T8
Installation Torque	240 lb-in
Recommended in-lb	
Plating Type	Unplated
UPC	781810079324

Dimensions

Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-1/3 in
Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm

Conductor Related

Conductor - Copper Solid Size Range	#4 AWG-2/0 AWG
-------------------------------------	----------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GBM_Lineart](#)
- [Sales Drawings - sc091658-01](#)
- [Specifications - GBM26T8](#)