



GBM34T4, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GBM34T4](#)



Mechanical Grounding Connector, Cable to 1/4" - 1/2" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud.

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810371701
UPC 12 Digit	7818103717011

Dimensions

Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	2-2/9 in
Dimension - Width inch	2.22 in
Dimension - Width mm	56 mm

Conductor Related

Conductor - Copper Solid Size Range	300 KCMIL - 500 KCMIL
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc091658-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GBM34T4-SPEC-EN | REV 1/2024