



# GBM39W, Mechanical Grounding Connector, Cable to Bar, Tin Plated

By Burndy  
Catalog # [GBM39W](#)



Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 550 kcmil - 750 kcmil, 5/8" Stud, Hot Tin Dipped.

### General

Catalog Number	GBM39W
Installation Torque	660 lb-in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
UPC	781810123614
UPC 12 Digit	7818101236144

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	3.31 in
Dimension - Height mm	84.1 mm
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width fraction	2-2/3 in
Dimension - Width inch	2.69 in
Dimension - Width mm	68 mm

### Conductor Related

Conductor - Copper Solid Size Range	550 KCMIL - 750 KCMIL
Conductor - Copper Str Size	550 kcmil;600 kcmil;700 kcmil;750 kcmil

Conductor - Copper Str Size Range	550 kcmil - 750 kcmil
-----------------------------------	-----------------------

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_GBM\\_Lineart](#)
- [Sales Drawings - sc091658-01](#)
- [Specifications - GBM39W](#)