



GC2929T8, Mechanical Grounding Connector, Two Cables to Bar

By Burndy
Catalog # GC2929T8



Mechanical Grounding Connector, 2 Cables to 1/2" - 1" Thick Bar;
2/0 AWG (Sol) -250 kcmil; 1/2" Stud; Torque: 480 in-lbs.

General

Catalog Number	GC2929T8
Installation Torque	480 lb-in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810001707
UPC 14 Digit GTIN	00781810001707

Dimensions

Dimension - Height inch	2.32 in
Dimension - Height mm	58.9 mm
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Width fraction	2 in
Dimension - Width inch	2.04 in
Dimension - Width mm	52 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 KCMIL
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil

Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
-----------------------------------	---------------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GC_Lineart](#)
- [Sales Drawings - sc091659-01](#)
- [Specifications - GC2929T8](#)