

GD1726TN, Mechanical Grounding Connector, 2 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GD1726TN](#)



Accommodates: 1-1/2" IPS; 1-5/8" - 1-7/8" Copper Rod; #4 Sol - 2/0 Str Conductor; Tin Plated; Direct Burial.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GD1726TN
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Electro Plated
U Bolt Type	268
UPC	781810343456
UPC 14 Digit GTIN	00781810343456

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height mm	0 mm
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	1.5

Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	1-5/8;1-3/4;1-7/8
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Specifications - GD1726TN](#)