

GD174CW, Mechanical Grounding Connector, 2 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GD174CW](#)



Cast Cu Ground Connector, 2 Cables to Rod or Tube, 1-1/2" IPS, 1-5/8" - 1-7/8" Rod, #8 Sol - #4 Str AWG Cu Cable, Tin plated, 3/8" Bolt.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

| | |
|------------------------------|--------------------------|
| Catalog Number | GD174CW |
| Installation Torque | 240 LBS/in |
| Recommended in-lb | |
| Material | Copper Alloy |
| Material Type - Screw Plated | DURIUM™ Silicon Bronze Y |
| Plating Type | Tin - Hot Dipped |
| U Bolt Type | 268 |
| UPC | 781810117477 |
| UPC 14 Digit GTIN | 00781810117477 |

Dimensions

| | |
|----------------------------|----------|
| Dimension - B Length inch | 1.31 in |
| Dimension - Height mm | 0 mm |
| Dimension - Width fraction | 3-1/4 in |
| Dimension - Width inch | 3.25 in |
| Dimension - Width mm | 83 mm |

Conductor Related

| | |
|-------------------------------------|-----------|
| Conductor - Copper Solid Size | 8;7;6;5;4 |
| Conductor - Copper Solid Size Range | 8-4 |
| Conductor - Copper Str Size | 8;7;6;5;4 |
| Conductor - Copper Str Size B Range | 1.5 |

| | |
|--|-------------------|
| Conductor - Copper Str Size Range | 8 AWG - 4 AWG |
| Conductor - Copper Tube Std Size | 1-5/8;1-3/4;1-7/8 |
| Conductor - Copper Tube Std Size Range | 1-5/8-1-7/8 |

Certifications And Compliance

| | |
|---|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - sd0137751](#)
[Specifications - GD174CW](#)