



GD1829W, Mechanical Grounding Connector, 2 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GD1829W](#)



Accommodates: 2 IPS 2" O.D. Tube; 2/0 Sol (.360 dia) - 250 kcmil (.575 dia) Copper.

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
U Bolt Type	257
UPC	781810099926
UPC 12 Digit	7818100999266

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-2/3 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Copper Solid Size Range	2/0;3/0;4/0
Conductor - Copper Str Size Range	2/0;3/0;4/0;250
Conductor - Copper Str Size Range	2
Conductor - Copper Tube Std Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size Range	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - SC002489-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GD1829W-SPEC-EN | REV 5/2024