



GD1929W, Mechanical Grounding Connector, 2 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GD1929W](#)



Accommodates: 2/0 Sol - 250 kcmil Copper Cables; 2-1/2" - 2-7/8" Rod; 2-1/2" IPS; Tin Plated.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GD1929W
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
U Bolt Type	266
UPC	781810117262
UPC 14 Digit GTIN	00781810117262

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height mm	0 mm
Dimension - Width fraction	4-1/5 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	2.5

Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	2-1/2
Conductor - Copper Tube Std Size Range	2-1/2

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - sd0137751](#)
[Specifications - GD1929W](#)



A Hubbell brand