



GD2026, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2026](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3" to 3-1/2" Rod, 3" Pipe.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

General

Catalog Number	GD2026
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	258
UPC	781810260388
UPC 14 Digit GTIN	00781810260388

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Dimension - Height mm	143 mm
Dimension - Width fraction	4-7/8 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	3



Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3
Conductor - Rod Size	3 in
Conductor - Rod Size Range	3 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GD2026_MODEL-PDF](#)
[3D Models - GD2026_MODEL-IGES](#)
[3D Models - GD2026_MODEL-STEP](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - SD..013775-01](#)
[Specifications - GD2026](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-GD2026-SPEC-EN | REV 3/2025