



# GD2029, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD2029](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 3" to 3-1/2" Rod, 3" Pipe.

## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

## General

|                       |                        |
|-----------------------|------------------------|
| Catalog Number        | GD2029                 |
| EU RoHS Indicator     | Yes                    |
| Installation Torque   | 240 LBS/in             |
| Recommended in-lb     |                        |
| Material              | Copper Alloy, Cast     |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Plated                | N                      |
| Plating Type          | Unplated               |
| Sub Brand             | MECHANICAL CONNECTOR   |
| Type                  | GD                     |
| U Bolt Type           | 258                    |
| UPC                   | 781810260395           |
| UPC 14 Digit GTIN     | 00781810260395         |

## Dimensions

|                             |          |
|-----------------------------|----------|
| Dimension - B Length inch   | 1.50 in  |
| Dimension - Height fraction | 5-5/8 in |
| Dimension - Height inch     | 5.63 in  |
| Dimension - Height mm       | 143 mm   |
| Dimension - Width fraction  | 4-7/8 in |
| Dimension - Width inch      | 4.81 in  |
| Dimension - Width mm        | 122 mm   |

## Conductor Related

|                                     |                 |
|-------------------------------------|-----------------|
| Conductor - Copper Solid Size       | 2/0;3/0;4/0     |
| Conductor - Copper Solid Size Range | 2/0-4/0         |
| Conductor - Copper Str Size         | 2/0;3/0;4/0;250 |

|  |                     |
|--|---------------------|
| Conductor - Copper Str Size B Range    | 3                   |
| Conductor - Copper Str Size Range      | 2/0 AWG - 250 kcmil |
| Conductor - Copper Tube Std Size       | 3                   |
| Conductor - Copper Tube Std Size Range | 3                   |

## Certifications And Compliance

|   |   |
|---|---|
| Buy America(n) Qualified                | TAA Compliant (All status valid till December 2024) |
| Certification - CSA Approved            | No  |
| Certification - ETL                     | No  |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No  |
| Certification - cULus                   | No  |
| Industry Standard(s)                    | UL467   |
| Standards - Industry Standards Met      | UL467   |
| Standards - RoHS Compliance             | EX  |
| Status                                  |   |
| UL Listed                               | Yes   |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[3D Models - GD2029\\_MODEL-STEP](#)  
[3D Models - GD2029\\_MODEL-IGES](#)  
[3D Models - GD2029\\_MODEL-PDF](#)  
[Catalogs - Burndy Grounding Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_gdla](#)  
[Sales Drawings - SD..013775-01](#)  
[Specifications - GD2029](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-GD2029-SPEC-EN | REV 3/2025