

GG151, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube

By Burndy
Catalog # [GG151](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 1" IPS.

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

General

Catalog Number	GG151
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	244
UPC	781810260043
UPC 14 Digit GTIN	00781810260043

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - Height mm	85.9 mm
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Rod Size	1 1/8 in; 1 1/4 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	16
-----------------------	----

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GG_LineArt](#)
[Sales Drawings - sd013776-01](#)
[Specifications - GG151](#)