

GG151SE, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube



By Burndy
Catalog # [GG151SE](#)

Cast Cu Alloy Ground Connector, 1" IPS, 1-1/8" - 1-1/4" Rod, 3/8" Bolt.

General

Catalog Number	GG151SE
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	244
UPC	781810042762
UPC 12 Digit	7818100427622

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Braid Width Max fraction	1 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Height inch	3.38 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Str Size B Range	1
Conductor - Copper Tube Std Size	1-1/8;1-1/4
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor Type	<ul style="list-style-type: none">Rod-SizeCU Tube Std-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ggla](#)
- [Sales Drawings - sd013776-01](#)
- [Specifications - GG151SE](#)