



GG161SE, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube

By Burndy
Catalog # GG161SE



RUN: IPS: 1-1/4" ROD: 1-3/8" - 1-1/2".

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	204
UPC	621945496804

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Braid Width Max fraction	1 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Height inch	3.50 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Copper Str Size B Range	1.25
Conductor - Copper Tube Std Size	1-1/2
Conductor - Copper Tube Std Size Range	1-1/2
Conductor Type	<ul style="list-style-type: none">Rod-SizeCU Tube Std-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd013776-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GG161SE-SPEC-EN | REV 1/2024