



# GG161W, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy  
Catalog # [GG161W](#)



RUN: IPS: 1-1/4" ROD: 1-3/8" - 1-1/2".

## General

|                                       |                             |
|---------------------------------------|-----------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in                  |
| Material                              | Copper Alloy                |
| Material Type - Screw Plated          | DURIUM™ Silicon Bronze<br>Y |
| Plating Type                          | Tin - Hot Dipped            |
| U Bolt Type                           | 204                         |
| UPC 12 Digit                          | 0                           |

## Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - B Length inch            | 1.38 in |
| Dimension - Braid Width Max fraction | 1 in    |
| Dimension - Braid Width Max inch     | 1.00 in |
| Dimension - Height inch              | 3.50 in |
| Dimension - Width fraction           | 3 in    |
| Dimension - Width inch               | 3.00 in |
| Dimension - Width mm                 | 76 mm   |

## Conductor Related

|                                        |                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------|
| Conductor - Copper Str Size B Range    | 1.25                                                                              |
| Conductor - Copper Tube Std Size       | 1-1/2                                                                             |
| Conductor - Copper Tube Std Size Range | 1-1/2                                                                             |
| Conductor Type                         | <ul style="list-style-type: none"><li>Rod-Size</li><li>CU Tube Std-Size</li></ul> |

## Certifications And Compliance

|                                         |       |
|-----------------------------------------|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| UL Listed                               | No    |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_ggla](#)  
[Sales Drawings - sd013776-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GG161W-SPEC-EN | REV 5/2024