



GG171W, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plate

By Burndy
Catalog # [GG171W](#)



Accommodates: 1-1/2" IPS; 1-5/8" - 1-7/8" Copper Rod.

General

| | |
|---------------------------------------|--------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in |
| Material | Copper Alloy |
| Material Type - Screw Plated | DURIUM™ Silicon Bronze Y |
| Plating Type | Tin - Hot Dipped |
| U Bolt Type | 199 |
| UPC | 781810207468 |
| UPC 12 Digit | 7818102074688 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - B Length inch | 1.38 in |
| Dimension - Braid Width Max fraction | 1 in |
| Dimension - Braid Width Max inch | 1.00 in |
| Dimension - Height inch | 3.50 in |
| Dimension - Width fraction | 3-1/4 in |
| Dimension - Width inch | 3.25 in |
| Dimension - Width mm | 83 mm |

Conductor Related

| | |
|--|---|
| Conductor - Copper Str Size B Range | 1.5 |
| Conductor - Copper Tube Std Size | 1-5/8;1-3/4;1-7/8 |
| Conductor - Copper Tube Std Size Range | 1-5/8-1-7/8 |
| Conductor Type | <ul style="list-style-type: none">Rod-SizeCU Tube Std-Size |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - UL Listed Direct Burial | Yes |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 12 |
|-----------------------|----|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd013776-01](#)



A proud member of the Hubbell Family.