



GG1815TN, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy
Catalog # [GG1815TN](#)



Mechanical Grounding Connector, Copper
Bar/Strap/Braid/Cable to Rod/Tube, 2"-2-3/8" Pipe.

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

General

Catalog Number	GG1815TN
Material	Copper Alloy, Cast, Tin Plated
Plated	Y
Plating Type	Tin Plated
U Bolt Type	257
UPC	621945455764
UPC 12 Digit	6219454557644

Dimensions

Dimension - Width inch	3.69 in
------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50066215](#)
- [Specifications - GG1815TN](#)