



# GG182TN, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy  
Catalog # [GG182TN](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2"-2 3/8" Pipe, 4.06 in Width. Tin Plated.

### Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

### General

Catalog Number	GG182TN
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast, Tin Plated
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Electro Plated
U Bolt Type	230
UPC	781810416754
UPC 14 Digit GTIN	00781810416754

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height mm	111.3 mm
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	10
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_ggla](#)  
[Sales Drawings - sd013776-01](#)  
[Specifications - GG182TN](#)