



GG182W, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy
Catalog # [GG182W](#)



Cast Cu Alloy Ground Connector, 2" IPS, 2" - 2-3/8" Rod, Tin plated, 1/2" Bolt.

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
U Bolt Type	230
UPC	621945552074

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Braid Width Max fraction	2 in
Dimension - Braid Width Max inch	2.00 in
Dimension - Height inch	4.38 in
Dimension - Width fraction	4 in
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Conductor Related

Conductor - Copper Str Size B Range	2
Conductor - Copper Tube Std Size	2;2-1/4
Conductor - Copper Tube Std Size Range	2-2-1/4
Conductor Type	<ul style="list-style-type: none">Rod-SizeCU Tube Std-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd013776-01](#)



A proud member of the Hubbell Family.