



GG192TN, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy
Catalog # [GG192TN](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2-1/2"-2 7/8" Pipe, 4.56 in Width. Tin Plated.

General

Material	Copper Alloy, Cast, Tin Plated
Plated	Y
Plating Type	Tin Plated
U Bolt Type	232
UPC	621945455771
UPC 12 Digit	6219454557711

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Width inch	4.56 in
Dimension - Width mm	116 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50066215](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GG192TN-SPEC-EN | REV 1/2024