

# GG222, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube



By Burndy  
Catalog # [GG222](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 4" Pipe, 4"-4-1/2" Rod, 6.19 W.

## Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

## Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

## General

Catalog Number	GG222
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GG
U Bolt Type	236
UPC	781810990070
UPC 12 Digit	7818109900700

## Dimensions

Dimension - B Length inch	2.00 in
---------------------------	---------

Dimension - Height mm	165.1 mm
Dimension - Width inch	6.19 in
Dimension - Width mm	157 mm

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus Certified Listed	No
	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_GG\\_LineArt](#)  
[Sales Drawings - 50116761](#)