



GG223TN, Mechanical Grounding Connector, Copper Bar, Strap, Braid, or Cable to Rod or Tube, Tin Plated

By Burndy
Catalog # [GG223TN](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 4"-4-1/2" Pipe, Bolt size: 1/2"; Tin Plated.

General

Catalog Number	GG223TN
Material	Copper Alloy, Cast, Tin Plated
Plated	Y
Plating Type	Tin Plated
U Bolt Type	236
UPC	621945455788
UPC 12 Digit	6219454557888

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	2.50 in
Dimension - Width inch	6.19 in
Dimension - Width mm	157 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50066215](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GG223TN-SPEC-EN | REV 6/2024