

GK1129, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1129](#)



Cast Cu Alloy Grounding Clamp, 3 Cables to Rod or Pipe, 1/2" Rod Dia, 1/4" IPS(A), 2/0 AWG Sol - 250 Kcmil Cu(AA).

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GK1129
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233689
UPC 14 Digit GTIN	00781810233689

Dimensions

Dimension - B Length inch	1.63 in
Dimension - Height inch	2.50 in
Dimension - Height mm	63.5 mm
Dimension - Width fraction	3-3/8 in
Dimension - Width inch	3.31 in
Dimension - Width mm	84 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	0.25
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil

Conductor - Copper Tube Std Size	0.5
Conductor - Copper Tube Std Size Range	0.5
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gk2la](#)
[Sales Drawings - sc069674-01](#)
[Specifications - GK1129](#)