



GK114C, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK114C](#)



Mechanical Grounding Connector, 3 Copper Cables to Rod or Pipe, 8 AWG (Sol) - 4 AWG (Str) Cu Cables, 1/4" Pipe, 1/2" Rod.

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233665
UPC 12 Digit	7818102336655

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.38 in
Dimension - Height inch	2.50 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

Conductor Related

Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Size	#8 AWG Sol - #4 AWG Str

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_gk21a](#)
[Sales Drawings - sc069674-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GK114C-SPEC-EN | REV 5/2024