



# GK1434, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy  
Catalog # [GK1434](#)



Mechanical Grounding Connector, 3 Cables to Rod or Pipe,  
300 kcmil - 500 kcmil, 1/2" - 3/4" Pipe, 7/8" - 1" Rod, 1/2" Stud.

## General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233696
UPC 12 Digit	7818102336966

## Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.75 in
Dimension - Height inch	3.69 in
Dimension - Width inch	4.10 in
Dimension - Width mm	104 mm

## Conductor Related

Conductor - Rod Size	7/8 in;1 in
Conductor - Rod Size Range	7/8 in-1 in
Conductor Size	300 kcmil - 500 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	696

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sc069674-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GK1434-SPEC-EN | REV 1/2024