

# GK1529, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy  
Catalog # [GK1529](#)



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Str.) - 250 kcmil, 1" Pipe, 1-1/8" - 1-1/4" Rod, 1/2" Stud.

### Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

### General

Catalog Number	GK1529
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233719
UPC 14 Digit GTIN	00781810233719

### Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	3.75 in
Dimension - Height mm	95.3 mm
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

### Conductor Related

Conductor - Rod Size	1 1/4 in
Conductor Size	2/0 AWG Str - 250 kcmil

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	4
-----------------------	---

### Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_gk2la](#)
- [Sales Drawings - sc069674-01](#)
- [Specifications - GK1529](#)