

GK1629, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # GK1629



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 1-1/4" Pipe, 1-3/8"- 1-1/2" Rod, 1/2" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GK1629
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233634
UPC 12 Digit	7818102336344

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	4.19 in
Dimension - Width inch	4.44 in
Dimension - Width mm	113 mm

Conductor Related

Conductor - Rod Size	1 1/2 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gk2la](#)
- [Sales Drawings - sc069674-01](#)
- [Specifications - GK1629](#)