

GK1729, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # GK1729



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 1-1/2" Pipe, 1-5/8" - 1-7/8" Rod, 1/2" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

| | |
|------------------------------|-----------------------------|
| Catalog Number | GK1729 |
| Installation Torque | 480 LBS/in |
| Recommended in-lb | |
| Material | Copper Alloy, Cast |
| Material Type - Screw Plated | DURIUM™ Silicon Bronze N |
| Plating Type | Unplated |
| Type | Three Cables to Rod or Tube |
| UPC | 781810233740 |
| UPC 12 Digit | 7818102337400 |

Dimensions

| | |
|---------------------------|---------|
| Bolt Size | 1/2 in |
| Dimension - B Length inch | 1.63 in |
| Dimension - Height inch | 4.63 in |
| Dimension - Width inch | 4.69 in |
| Dimension - Width mm | 119 mm |

Conductor Related

| | |
|----------------------------|----------------------------|
| Conductor - Rod Size | 1 5/8 in;1 3/4 in;1 7/8 in |
| Conductor - Rod Size Range | 1 5/8 in-1 7/8 in |
| Conductor Size | 2/0 AWG Sol - 250 kcmil |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 8 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gk2la](#)
- [Sales Drawings - sc069674-01](#)
- [Specifications - GK1729](#)