



# GK1826W, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GK1826W](#)



Accommodates: 2" IPS; 2" - 2-3/8" Rod; #4 Sol - 2/0 Str  
Copper Cable; Tin Plated.

## General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
U Bolt Type	257
UPC	781810117583
UPC 12 Digit	7818101175833

## Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	4.19 in
Dimension - Width fraction	4-5/9 in
Dimension - Width inch	4.56 in
Dimension - Width mm	116 mm

## Conductor Related

Conductor - Copper Solid Size Range	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Str Size Range	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	2
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	2;2-1/4;2-1/2;2-3/4
Conductor - Copper Tube Std Size Range	2-2-3/4

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_gk2la](#)  
[Sales Drawings - sc069674-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GK1826W-SPEC-EN | REV 5/2024