



GK1829CG1, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1829CG1](#)

Accommodates: 2/0 Sol - 250 kcmil Copper Cable; Torque: 240 in-lbs.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GK1829CG1
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	621945014237
UPC 14 Digit GTIN	00621945014237

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.62 in
Dimension - Height inch	2.81 in
Dimension - Height mm	71.4 mm
Dimension - Width fraction	5-1/4 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Conductor Related

Conductor Size	2/0 AWG Sol - 250 kcmil
----------------	-------------------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - CSC.018465-01](#)
[Specifications - GK1829CG1](#)