

GK1926W, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GK1926W](#)



Accommodates: 2-1/2" IPS; 2-1/2" - 2-7/8" Rod; #4 Sol - 2/0 Str Copper Cable; Tin Plated.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GK1926W
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
U Bolt Type	266
UPC	781810117576
UPC 12 Digit	7818101175766

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	5 in
Dimension - Width inch	5.06 in
Dimension - Width mm	129 mm

Conductor Related

Conductor - Copper Solid Size Range	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size	4-3/0
Conductor - Copper Str Size Range	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B	2.5
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	2;2-1/4;2-1/2;2-3/4
Conductor - Copper Tube Std Size Range	2-2-3/4

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gk2la](#)
- [Sales Drawings - sc069674-02](#)
- [Specifications - GK1926W](#)



A Hubbell brand