



GK2034, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK2034](#)



Mechanical Grounding Connector, 3 Cables to Pipe or Rod,
300 kcmil - 500 kcmil, 3" Pipe, 3 or 3-1/2" Rod, 1/2" Stud.

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	621945128842
UPC 12 Digit	6219451288422

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.75 in
Dimension - Height inch	6.31 in
Dimension - Width fraction	6-7/8 in
Dimension - Width inch	6.88 in
Dimension - Width mm	175 mm

Conductor Related

Conductor - Rod Size	3 in ; 3 1/2 in
Conductor Size	300 kcmil - 500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_gk2la](#)
[Sales Drawings - sc069674-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GK2034-SPEC-EN | REV 5/2024