

GK2129, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK2129](#)



Mechanical grounding connector; 3 cables to rod or pipe; 2/0 AWG Solid - 250 kcmil; 3-1/2" Pipe; 3-1/2" to 4" Rod; 1/2" Stud; UL467.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GK2129
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810196281
UPC 12 Digit	7818101962811

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.50 in
Dimension - Height inch	6.16 in
Dimension - Width fraction	6-5/7 in
Dimension - Width inch	6.72 in
Dimension - Width mm	171 mm

Conductor Related

Conductor - Rod Size	3 1/2 in; 4 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gk2la](#)
- [Sales Drawings - sc069674-02](#)
- [Specifications - GK2129](#)