



GK2226W, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GK2226W](#)



Accommodates: 4 Sol - 2/0 Str Copper Cable; Tin Plated.

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
UPC	781810135204
UPC 12 Digit	7818101352044

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	6.38 in
Dimension - Width fraction	6-2/3 in
Dimension - Width inch	6.69 in
Dimension - Width mm	170 mm

Conductor Related

Conductor - Copper Solid Size Range	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Str Size Range	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	4;4 1/2
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_gk2la](#)
[Sales Drawings - sc069674-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GK2226W-SPEC-EN | REV 5/2024