



# GK2226W, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GK2226W](#)



Accommodates: 4 Sol - 2/0 Str Copper Cable; Tin Plated.

### General

Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
UPC	781810135204
UPC 12 Digit	7818101352044

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	6.38 in
Dimension - Width fraction	6-2/3 in
Dimension - Width inch	6.69 in
Dimension - Width mm	170 mm

### Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	4;4 1/2
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_gk2la](#)  
[Sales Drawings - sc069674-02](#)



A proud member of the Hubbell Family.