

## GK2229, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy  
Catalog # [GK2229](#)



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 4" Pipe, 4" - 4-1/2" Rod, 1/2" Stud.

### Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

### General

Catalog Number	GK2229
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810079225
UPC 14 Digit GTIN	00781810079225

### Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	6.81 in
Dimension - Height mm	173 mm
Dimension - Width fraction	7-1/4 in
Dimension - Width inch	7.25 in
Dimension - Width mm	184 mm

### Conductor Related

Conductor - Rod Size	4 in; 4 1/2 in;
Conductor Size	2/0 AWG Sol - 250 kcmil

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_gk2la](#)  
[Sales Drawings - sc069674-02](#)  
[Specifications - GK2229](#)