


GK6429, Copper Alloy Grounding Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK6429](#)



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 3/8" Pipe, 5/8"-3/4" Rod.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining Three Equal Copper Cables To Rod Or Tube, Direct Burial In Earth Or Concrete

General

Catalog Number	GK6429
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	Three Cables to Rod or Tube
UPC	781810233535
UPC 12 Digit	7818102335355

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	2.88 in
Dimension - Width fraction	3-1/2 in
Dimension - Width inch	3.50 in
Dimension - Width mm	89 mm

Conductor Related

Conductor - Rod Size	5/8 in ; 3/4 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GK6429_MODEL-PDF](#)
- [3D Models - GK6429_MODEL-IGES](#)
- [3D Models - GK6429_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gk2la](#)
- [Sales Drawings - sc069674-01](#)