

GKA25SB, Ground Connector for Copper, Silicon Bronze Hardware

By Burndy
Catalog # [GKA25SB](#)



Accommodates: #4 Str - 1/0 Str; Recommended Torque: 200 in-lbs; silicon bronze hardware.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

General

Catalog Number	GKA25SB
Installation Torque	200 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	KA-LUG™
UPC	781810569580
UPC 12 Digit	7818105695800

Dimensions

Dimension - B Length inch	.69 in
Dimension - Height inch	.94 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - N inch	0.38 in
Dimension - Pad Width inch	0.75 in

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Str Size Range	4 AWG-1/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50017297](#)
- [Specifications - GKA25SB](#)