



# Gasoline Hydraulic Pump, 4 HP, 8 Quarts Reservoir Volume, 10000 psi

By Burndy  
Catalog # [GP10](#)

Pump, Gasoline, 10K psi, 4 HP, 8 Quarts.



## Features

- Heavy duty gasoline engine
- Sturdy steel roll cage design
- Manual control valve
- Quick disconnect hydraulic coupler
- 8 quart reservoir
- Oil level inspection window

## Application

Pumping

## General

|                          |   |
|--------------------------|---|
| Application - For Use On | Use with 10,000 psi Remote Hydraulic Crimpers and Cutters |
| EU RoHS Indicator        | Yes   |
| Power Source             | 4 HP; 4 Cycle Engine                                      |
| Tool Type                | Pump, Gas Hydraulic                                       |
| Type                     | Pump  |
| UPC                      | 781810492758  |
| UPC 12 Digit             | 7818104927588   |

## Dimensions

|            |                                |
|------------|--------------------------------|
| Dimensions | 21.00 in x 16.00 in x 22.25 in |
| Height     | 22.25 in                       |
| Length     | 21 in                          |
| Weight     | 78 lb                          |
| Width      | 16 in                          |

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

|                       |           |
|-----------------------|-----------|
| Minimum Pack Quantity | 1         |
| Package Contents      | Pump only |

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OWPF\\_GP10\\_lineart](#)  
[Sales Drawings - SE..207683-01](#)  
[SDS - ALFLUID SDS \(GHS\) \(2021-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GP10-SPEC-EN | REV 5/2024