



GP1526G1, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1526G1](#)

Raised Floor Grounding Clamp, #8 Sol. - 2/0 Str., 1.69 in L, 2.62 in W.



General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round
Plated	N
Plating Type	Unplated
U Bolt Type	UB244
UPC	781810042823
UPC 12 Digit	7818100428233

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

Conductor Related

Conductor Size	#8 Sol AWG - 2/0 Str AWG
Number of Conductors	1;2

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GP1526G1_MODEL-PDF](#)
[3D Models - GP1526G1_MODEL-STEP](#)
[3D Models - GP1526G1_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_GP_LineArt](#)
[Sales Drawings - sd201549-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GP1526G1-SPEC-EN | REV 5/2024