



## GP1526G1, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GP1526G1](#)

Raised Floor Grounding Clamp, #8 Sol. - 2/0 Str., 1.69 in L, 2.62 in W.



### General

|                                       |                        |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in             |
| Material                              | Copper Alloy, Cast     |
| Material - Hardware                   | DURIUM™ Silicon Bronze |
| Pedestal Type                         | Round                  |
| Plated                                | N                      |
| Plating Type                          | Unplated               |
| U Bolt Type                           | UB244                  |
| UPC                                   | 781810042823           |
| UPC 12 Digit                          | 7818100428233          |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Bolt Size                       | 3/8 in  |
| Dimension - B Length inch       | 1.75 in |
| Dimension - L Length Overall mm | 43 mm   |
| Dimension - Length Overall inch | 1.69 in |
| Dimension - Width inch          | 2.62 in |
| Dimension - Width mm            | 67 mm   |

### Conductor Related

|                      |                          |
|----------------------|--------------------------|
| Conductor Size       | #8 Sol AWG - 2/0 Str AWG |
| Number of Conductors | 1;2                      |

### Certifications And Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - UL Listed Direct Burial | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### Product Assets

[3D Models - GP1526G1\\_MODEL-STEP](#)  
[3D Models - GP1526G1\\_MODEL-PDF](#)  
[3D Models - GP1526G1\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_GP\\_LineArt](#)  
[Sales Drawings - sd201549-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GP1526G1-SPEC-EN | REV 5/2024