



GP154C, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP154C](#)

Mechanical Grounding Connector, 2 Cables to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 1" Pipe, 1 1/8" - 1 1/4" Rod, 3/8" Stud.



General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	191
UPC	621945145702
UPC 12 Digit	6219451457022

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Rod Size Range	1 1/8" - 1 1/4"
Conductor Size	#8 AWG SOL - 4 AWG STR

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_gpla](#)
[Sales Drawings - SD..013778-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GP154C-SPEC-EN | REV 5/2024