



GP164C, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP164C](#)

Accommodates: 1-1/4" IPS; 1-3/8" - 1-1/2" Rod; #8 Sol - #4 Str Copper Cable.



General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	204
UPC	781810117613
UPC 12 Digit	7818101176133

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.88 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Rod Size Range	1 3/8" - 1 1/2"
Conductor Size	#8 AWG SOL - 4 AWG STR

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_gpla](#)
[Sales Drawings - SD..013778-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GP164C-SPEC-EN | REV 5/2024