



# GP1826, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GP1826](#)

Mechanical grounding connector, 2" Pipe Size, 2" Rod Size, 4 SOL - 2/0 STR Wire Size, 240 LBS/in Installation Torque.



## General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	257
UPC	781810079171

## Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	2.75 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	3-11/16 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

## Conductor Related

Conductor - Rod Size	2 in
Conductor Size	#4 Sol AWG - 2/0 Str AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	12
-----------------------	----

## Product Assets

[3D Models - GP1826\\_MODEL-IGES](#)  
[3D Models - GP1826\\_MODEL-PDF](#)  
[3D Models - GP1826\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..013778-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GP1826-SPEC-EN | REV 1/2024