



GP1926, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1926](#)

Mechanical grounding connector, 2 1/2" Pipe Size, 2 1/2" Rod Size, 4 SOL - 2/0 STR Wire Size, 240 LBS/in Installation Torque.



General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	266
UPC	781810158630

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	3.25 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	4-3/16 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

Conductor Related

Conductor - Rod Size	2 1/2 in
Conductor Size	#4 AWG Solid - 2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1152

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_gpla](#)
[Sales Drawings - SD..013778-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GP1926-SPEC-EN | REV 5/2024