



# GP64526G1, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GP64526G1](#)

Raised Floor Grounding Clamp, #4 Sol. - 2/0 Str., 1.69 in L, 2.38 in.



## Application

For Raised Floor Systems

## General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GP-G1
U Bolt Type	UB222
UPC	781810828014
UPC 12 Digit	7818108280144

## Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

## Conductor Related

Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Size	#4 AWG Sol - 2/0 AWG Str
Conductor Type	CU C Str-Size
Number Of Conductors	1;2

## Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - GP654CG1\\_MODEL-PDF](#)  
[3D Models - GP654CG1\\_MODEL-STEP](#)  
[3D Models - GP654CG1\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd201549-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GP64526G1-SPEC-EN | REV 1/2024