



GP654CG1, Raised Floor Grounding Clamp

By Burndy
Catalog # [GP654CG1](#)

Raised Floor Grounding Clamp, #8 Sol. - 4 Str., 1.31 in L, 2.38 in.



Application

For Raised Floor Computer Grounding Applications

General

Catalog Number	GP654CG1
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GP-G1
U Bolt Type	UB222
UPC	781810828007
UPC 12 Digit	7818108280077

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Conductor Related

Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor Size	#8 AWG Sol - #4 AWG Str
Number of Conductors	1;2

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GP654CG1_MODEL-PDF](#)
- [3D Models - GP654CG1_MODEL-STEP](#)
- [3D Models - GP654CG1_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gpla](#)
- [Sales Drawings - sd201549-01](#)
- [Specifications - GP654CG1](#)



A Hubbell brand