



GRC3426, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC3426](#)



ROD: 5/8" & 3/4" WIRE/CABLE MIN.: 8 SOL. WIRE/CABLE MAX.: 2/0 STR.

General

Catalog Number	GRC3426
Installation Torque	170 in-lb
Recommended in-lb	
Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810424292
UPC 14 Digit GTIN	00781810424292

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	0.65 in
Dimension - Height mm	0 mm

Conductor Related

Conductor - Rod Size	5/8 in , 3/4 in
Conductor Size	#8 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none">Rod-SizeCU C Solid-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GRC_Lineart](#)
- [Sales Drawings - CSC028819-01](#)
- [Specifications - GRC3426](#)



A Hubbell brand